# TIP-ON BLUMOTION for LEGRABOX

## Sink pull-out



www.blum.com



#### **TIP-ON BLUMOTION in sink pull-out**

The sink pull-out uses every inch of storage space available and gives you easy access to the contents. With TIP-ON BLUMOTION, it is now mechanically possible to open LEGRABOX sink pull-outs with just a light touch and close them silently and effortlessly.

#### Don't waste an inch

The U-shaped sink pull-out puts the space around the sink to best possible use. It's ideal for clearing away sponges, washing-up liquid and tabs. It keeps worktops free and ensures that cleaning products are easily accessible. Also suitable for pull-outs with a drain cut-out in the bathroom.



One-touch opening, feather-light glide, silent and effortless closing. TIP-ON BLUMOTION is a marriage of perfect motion and enhanced user convenience. The motion is

assisted 100% mechanically.

TIP-ON BLUMOTION can be implemented with a small front gap of 2.5 mm.



Learn more about TIP-ON BLUMOTION for LEGRABOX at:

www.blum.com/tob\_lbx



Ease of use

### **TIP-ON BLUMOTION** for LEGRABOX

## Exceptional ease of use with the sink pull-out

**Ablum** 

#### Set containing TIP-ON BLUMOTION unit and TIP-ON BLUMOTION latch




#### **Order specification**

1	TIP-ON BLUMOTION set for sink pull-out*						
1.				Weight (kg)**			
	NL (mm)	Unit		< 10 kg	20 kg	30 kg	40 kg
and the second	350-600	L1***	T60L9340	≤ 20			
¢.		L3	T60L9540			15–40	
	Consisting of: 2x TIP-ON BLUMOTION unit 2x TIP-ON BLUMOTION latch 2x synchronisation adapter LW ≥ 314 mm		<ul> <li>* Possible for NL ≥ 350 mm</li> <li>** Recommended weight ranges (total weight of pull-out) for optimum opening and closing function</li> <li>*** Can only be combined with 40 kg cabinet profile (750.)</li> </ul>				
Make the right calculations for your TIP-ON BLUMOTION unit using the product configurator: www.blum.com/configurator							

	2	TIP-ON BLUMOTION synchronisation linkage				
		Possible for LW ≥ 314 mm				
		Suitable for LW up to 1370 mm				
			T60.1125W			


#### Planning

#### Space requirements in the cabinet - drawer/high fronted pull-out



 $^{\ast}\,$  + 1 mm for assembly of the cabinet profile on the horizontal cabinet side  $^{\ast\ast}\,$  incl. 2 mm tilt adjustment


Space requirements in the cabinet - inner drawer




 $^{\star}\,$  + 1 mm for assembly of the cabinet profile on the horizontal cabinet side

Latch set (ZI7.0M07): Cannot be used in combination with TIP-ON BLUMOTION

#### Synchronisation



Distance between the synchronisation linkage and the front



ionisation ninkaye and the nont								
	NL (mm)	X for 750.xxx1 <mark>S</mark>	X for 750.xxx1M					
	350	65 mm	80 mm					
	400	85 mm	100 mm					
	450	65 mm	80 mm					
	500	65 mm	80 mm					
	550	65 mm	80 mm					
	600	65 mm	80 mm					